SIEMENS

Document No. 149-820 September 18, 2013



Series 2200 Temperature Room Units for TEC and ATEC



Figure 1. QAA2280.FWSC Temperature Room Unit.

The Series 2200 Temperature Room Units from Siemens Industry, Inc. offer a wide range of features and functionality that work in concert with the APOGEE® Automation System to deliver exceptional occupant comfort in even the most demanding application environments. The product family includes plain, sensing-only variants, and fully interactive types with a graphical OLED (Organic Light Emitting Diode) displays. All room units incorporate precision temperature sensing elements to accurately and reliably measure room temperature. Their compact, low profile design results in an attractive. inconspicuous installation. Strategically placed ventilation slots in the housing optimize airflow through the cover for fast measurement response and superior control.

These room units provide accurate, reliable sensing of room temperature and some models also sense humidity. They can be used with Terminal Equipment Controllers (TECs) and Actuator Terminal Equipment Controllers (ATECs).

NOTE: Standard P1 TECs, and all ATECs do not

have the ability to handle humidity data. If humidity is needed for monitoring or control, use the QFA3280 versions of this room unit line with a BACnet TEC.

NOTE: If there isn't an RM CO2 point in the

BACnet TEC, the sensor will display the CO₂, but it will not be available at the BACnet TEC.

For those sensors that support relative humidity, if there isn't an RM RH point, the sensor will display RM and RH, but it will not be available at the BACnet TEC.

Applications

The Series 2200 Temperature Room Unit applications incorporate a digital temperature sensor integrated circuit and plug-in HMI (Human-Machine Interface) port located on the bottom of the cover. The HMI port provides a convenient means of communicating with the controller to command or troubleshoot the system. These room units connect to the controller via a sixwire cable terminated with a plug-in RJ-11 connector. The cable transmits the temperature, the communication with the HMI, and the optional setpoint and override signals.

Siemens Industry, Inc. Page 1 of 3

Available Features (QxAxxxx.F models only)

- Organic Light Emitting Diode Display: A 96 x 64 pixel graphical OLED allows simultaneous digital display of room temperature, and day/night operation status.
 - Standard Display Features:
 - Display of operating mode: Graphic symbols are displayed to indicate the controller's operating mode. A person in the house indicates occupied mode operation and a person outside the house indicates unoccupied mode.
 - Easy-to-read room temperature value to 1 decimal place.
 - Easy-to-read room humidity value (QFA models only).
 - · Digital display.
 - Configurable Display Features:
 - · Degrees Fahrenheit or Celsius,
 - · Graphical or alphanumeric setpoint display.
 - · Room temperature display on or off.
 - Room humidity display on or off (QFA models only).
- Digital setpoint adjustment: The room unit's keypad allows error-free digital setpoint adjustments in one-degree increments. Setpoint values momentarily display as changes are made.
- Override button: The override button allows an occupant to change to an occupied control schedule during the unoccupied cycle for a predetermined time period as defined by the controller. Occupancy graphic is shown on the display during occupied time periods.
- Maintenance-free: These room units draw a small amount of power directly from the controller.
- Backward compatibility: These room units are backward compatible with all TECs. The room units are wired with six-conductor phone cables and standard RJ-11 connectors.
- HMI port: RJ-11 connection allows laptop connection for commissioning and servicing the controller.

Specifications

| 55°F to 95°F |
|--|
| (13°C to 35°C) |
| 55°F to 95°F |
| (13°C to 35°C) |
| 0% to 100% rh |
| |
| Proprietary digital protocol (.D, .F types) Resistive (QAAxxxx.E |
| types). |
| Digital Temperature Sensor IC (.D,.F types) 10K Ohm NTC Type 2 thermistor (QAAxxxx.E types) |
| |
| ement |
| |
| <u>+</u> 0.9°F (±0.5°C) |
| <u>+</u> 0.5°F (±0.3°C) |
| ent |
| ±0.5°F (±0.3°C) |
| ±1.0°F (±0.55°C) |
| |
| |
| ± 2% rh |
| ± 4% rh |
| A. II |
| Adjustable to +/- 5°F Adjustable to +/- 5% rh |
| Adjustable to 17 070 III |
| 100 ft. Maximum cable |
| length. |
| 6C #24 AWG, Belden |
| DFLEX3 or equal, NEC Class 2 |
| None required |
| |
| 4.5" × 2.75" × 1.18" (115 mm × 70 mm × 30 mm) |
| White |
| Supplied by TEC or ATEC |
| |

Page 2 of 3 Siemens Industry, Inc,

Product Ordering Information

| Part Number | Comm Type | Comm Type | Logo | Display | Setpoint/ Occupancy | Temp | RH (2%) |
|--------------|--------------|--------------|---------|---------|------------------------|------|------------|
| QAA2280.EWSC | Analog | Resistive | | | | • | |
| QAA2280.DWSC | Digital | | | • | | • | |
| QAA2280.FWSC | | | Siemens | • | • | • | |
| QFA3280.EWSC | | P1 | Siemens | | | • | • |
| QFA3280.DWSC | | | | • | | • | • |
| QFA3280.FWSC | | | | • | • | • | • |
| QAA2280.EWNC | Analog | Resistive | | | | • | |
| QAA2280.DWNC | Digital | | | • | | • | |
| QAA2280.FWNC | | | None | • | • | • | |
| QFA3280.EWNC | | P1 | inone | | | • | • |
| QFA3280.DWNC | | | | • | | • | • |
| QFA3280.FWNC | | | | • | • | • | • |

Accessories Ordering Information

| Description | Product Part Number |
|--|---------------------|
| 25-foot (7.6 m) cable with connections | 588-100A |
| 50-foot (15.2 m) cable with connections | 588-100B |
| 100-foot (30.5 m) cable with connections | 588-100C |
| Passkey Tool (Used to set room unit parameters) | 544-643A |
| Replacement rh 2%+ Thermostat Element – TEC Room Unit | AQF3060 |
| Replacement Housing Base | 563-102-01 |
| Room Unit Back Plate (10-pack) | AQA2200-INTL |
| Room Unit Back Plate (Single) | AQA2200-2X4 |
| Room Sensor Insulating Gasket (10-pack) (Recommended for hollow wall installations.) | 563-102 GSKT KIT |

Information in this document is based on specifications believed correct at the time of publication. The right is reserved to make changes as design improvements are introduced. APOGEE is a registered trademark of Siemens Industry, Inc. Other product or company names mentioned herein may be the trademarks of their respective owners. © 2013 Siemens Industry, Inc.